

Professional Packaging Systems

2010 S. Great Southwest Parkway Grand Prairie, Texas 75051 www.ProPac.com Contact

Our Packaging Experts solutions@propac.com 888-318-0083

Starview SP Semi-Auto Stationary Heat Skin Packaging Machine



At a Glance

- Designed for low to medium volume applications
- SP models have a stationary heating system with instant on/off heaters
- SP-IR models incorporate an automatic retractable radiant heater panel system
- PLC timer control for precision repeatability

Buy your skin packaging materials from us, and get a discount on this Starview skin packager!

Pricing

Call us at 888-318-0083

Many options are available. Complete details will need to be finalized to determine requirements and final system costs. Work with your Pro Pac representative to build this machine to your specifications.

Medium Volume Stationary Heat Skin Packaging Machines

Starview SP and SP-IR Series skin packaging machines are designed for low to medium volume applications. SP machines incorporate a stationary heating system with instant on/off heaters. SP-IR models incorporate an automatic retractable radiant heater panel system, controlled by percentage controllers for precise heat distribution.

All SP and SP-IR skin packaging machines have PLC timer control for precision repeatability and an accurate turbine regulator. An infeed table, out-feed table and impulse type hot wire cut-off are all standard.

These skin packaging machines can be equipped with a three-stage vacuum system for products with complex shapes. The SP-IR series may be ordered with a blister forming option to produce low-profile blisters from roll stock.

Features of the SP and SP-IR Series

Standard sizes 18" x 24" through 36" x 48" offered Use for retail carded packaging or shipping containment PLC machine control with touch screen operator interface panel Infeed and outfeed tables standard Impulse hot wire cut-off standard Heavy-duty industrial design for long life

Please contact Pro Pac or call 888-318-0083 for your skin packaging equipment.

Specifications of the SP Skin Packaging Machines

Specifications	SP-1824	SP-2430		SP-2436		SP-2448
Max Card Size	18" x 24"	24" x 30"		24" x 36"		24" x 48"
Max Product Height	10"	10"		10"		10"
Heating System	Quartz impulse	Quartz in	npulse	Quartz impulse		Quartz impulse
Light Curtain	Optional	Optional		Optional		Standard
Average Cycle	15 - 60 seconds	15 - 60 se	conds	15 - 60 seconds		15 - 60 seconds
Electrical	208-240V, 3 ph, 32 amps	208-240V amps	, 3 ph, 55	208-240V, 3 ph, amps	70	208-240V, 3 ph, 100 amps
Specifications	SP-3036		SP-3048		SP-3	648
Max Card Size	30" x 36"		30" x 48"		36" x	< 48"
Max Product Heigh	nt 10"		10"		10"	
Heating System	Quartz impulse		Quartz imp	oulse	Quai	rtz impulse
Light Curtain	Standard		Standard		Stan	dard
Average Cycle	15 - 60 seconds		15 - 60 sec	onds	15 - 6	60 seconds
Electrical 208-240V, 3 ph, 80		30 amps	amps 208-240V, 3 ph, 90 amps		208-240V, 3 ph, 100 amps	

Specifications of the SP-IR Skin Packaging Machines

Specifications	SP-IR-1824	SP-IR-2430	SP-IR-2436	SP-IR-3036
Max Card Size	18" x 24"	24" x 30"	24" x 36"	30" x 36"
Max Product Height	10"	10"	10"	10"
Heating System	Radiant panel	Radiant panel	Radiant panel	Radiant panel
Light Curtain	Standard	Standard	Standard	Standard
Average Cycle	15 - 45 seconds			
Electrical	208-230V, 3 ph, 50 amps	208-230V, 3 ph, 55 amps	208-230V, 3 ph, 70 amps	208-230V, 3 ph, 80 amps

Please contact Pro Pac or call 888-318-0083 for your skin packaging equipment.